



WNA300B



Blind switch insert 1p rocker 2g+impr.ed symb.arrow surf.-/flushmtd,W.1,p.wh. LT

Technical Features

Materials

Colour	Polar white
RAL code	9010

Controls and indicators

Venetian blind switch type	1-pole switch
----------------------------	---------------

Materials

Surface finish	Matt
Contains recycled material (% of total plastic weight)	0 %
Material	Thermoplastic
Treatment	Untreated

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Switching current	10 A
Switching current	10 A

Safety

Ingress Protection (IP) class	IP55
Locking type	Without lock

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Switch mode	With mechanical and electrical interlock to prevent mutual switch-on
Type of connection	With plug-in terminals
Installation mode	With mounting adapter

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Equipment

Is key removable	No
------------------	----

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes