




WNA408

Frame 2gang vertical for flush-mounted installation, with sealing W.1 light grey

Technical Features

Capacity

Number of gangs	2
Number of modules	2

Materials

Colour	Grey
RAL code	Similar to RAL 7035
Surface finish	Matt
Material	Thermoplastic
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

Dimensions

Height	83 mm
Width	154 mm
Depth	38 mm

Accessories

Has labelling field	No
---------------------	----

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Vertical

Safety

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP55 with closed cover
Impact resistance IK	IK07

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For vertical mounting
Screws/screwdriver	With screwdriver

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes