



WNA602



Insert of LED signal light, blue lighting surface-mtd/flush-mtd, W.1, grey matt

**Technical Features**

**Voltage**

Rated voltage	230 V
---------------	-------

**Power**

Power absorbed	0 W
----------------	-----

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Lighting**

Type of lamp	LED
--------------	-----

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Depth	48 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Safety**

Ingress Protection (IP) class	IP55
-------------------------------	------

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Suitable for**

cubyko	
--------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes