




WNA602



**Insert of LED signal light, blue lighting surface-mtd/flush-mtd, W.1, grey matt**

**Technical Features**

**Voltage**

Rated voltage 230 V

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Depth 48 mm

**Connectivity**

Mounting type Screw mounting

**Safety**

Ingress Protection (IP) class IP55

**Use conditions**

Operating temperature -15 - 30 °C

**Suitable for**

cubyko

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes