



WNA603



Insert of LEDsignal light, white lighting surface-mtd/flush-mtd, W1, grey matt

Technical Features

Voltage

Rated voltage	230 V
---------------	-------

Power

Power absorbed	0 W
----------------	-----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Lighting

Type of lamp	LED
--------------	-----

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	48 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Imprint	Without imprint
---------	-----------------

Suitable for

cubyko

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----