



WNA603



Insert of LEDsignal light, white lighting surface-mtd/flush-mtd, W.1, grey matt

Technical Features

Voltage

|               |       |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Lighting

|              |     |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Materials

|                |               |
|----------------|---------------|
| Colour         | Grey          |
| RAL code       | 7011          |
| Surface finish | Matt          |
| Material       | Thermoplastic |
| Treatment      | Untreated     |

Dimensions

|        |       |
|--------|-------|
| Height | 71 mm |
| Width  | 71 mm |
| Depth  | 48 mm |

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
|-------------------------------|------|

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

Texts

|         |                 |
|---------|-----------------|
| Imprint | Without imprint |
|---------|-----------------|

Suitable for

|        |  |
|--------|--|
| cubyko |  |
|--------|--|

Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |