



WNA683

IP55

Surface-mounted lower casing 3gang hor., w. frame and cable entries W.1 grey

Technical Features

Capacity

Number of modules	3
-------------------	---

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

Dimensions

Number of units	3
Height	76 mm
Width	218 mm
Depth	56 mm
Built-in depth	65 mm

Equipment

With cable entry	Yes
------------------	-----

Installation, mounting

Mounting-/Connection Position	Horizontal
Mounting on	Surface mounting

Accessories

With frame cover	Yes
------------------	-----

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK08

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Safety

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

Texts

Installation mode	For horizontal mounting
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Suitable for

cubyko	
cubyko	

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes