



WNC001B

IP55

Change-over switch surface-mtd, W.1, p. white, matt, plastic LT

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Contains recycled material (% of total plastic weight) 0 %

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 76 x 76 mm

Built-in depth 65 mm

Built-in depth flush-mounted boxes 0 mm

Height of P-touch band for labelling field 0 mm

Safety

Impact resistance IK IK08

Usable in higher IP class IP55 with closed cover

Electric current

Rated current 10 A

Connection

Connector/plug type Plug-in terminal

Texts

Installation mode For screw fastening

Type of connection With plug-in terminals

Push button No

Imprint Without imprint

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes