



WNC020



Push-button, NO contact surface-mtd, W1, grey/light grey matt LT

Technical Features

Electric current

Momentary contact current

10 A

Voltage

Rated voltage

250 V

Frequency

Frequency

50 - 60 Hz

Architecture

Control/operation element

Single rocker

Number of poles

1

Materials

Colour

Grey

Surface finish

Matt

Material

Thermoplastic

Treatment

Untreated

Transparent

No

Dimensions

Height

76 mm

Width

75 mm

Depth

64 mm

Built-in depth flush-mounted boxes

0 mm

Installation, mounting

Mounting on

Surface mounting

Controls and indicators

Number of buttons

1

Type of push button

Single push button

With feedback signal contact

No

Safety

Ingress Protection (IP) class

IP55

Impact resistance IK

IK08

Accessories

Has labelling field

No

Use conditions

Operating temperature

-25 - 35 °C

Texts

Imprint

Without imprint

Installation mode

For screw fastening

Sealing

With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Terminal

With Wago clip-in 2-wire connection terminal for wiring
With two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection

With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes