



WNC020



**Push-button, NO contact surface-mtd, W.1, grey/light grey matt LT**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Single rocker
Number of poles	1

**Materials**

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Backside internal	Matt

**Dimensions**

Height	76 mm
Width	75 mm
Depth	64 mm
Built-in depth flush-mounted boxes	0 mm
Height of P-touch band for labelling field	0 mm

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Controls and indicators**

Indicator lamp	Without
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Connectivity**

With claw mounting	No
--------------------	----

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK08

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-25 - 35 °C
-----------------------	-------------

**Texts**

Installation mode	For screw fastening
Sealing	With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside
Switch mode	Change-over

---

**Texts**

Terminal	With Wago clip-in 2-wire connection terminal for wiring
	With two clip-in places for Wago 2-wire connection terminals in the housing floor
Type of connection	With plug-in terminals

---

**Suitable for**

cubyko

---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes