



WNC035



**Key switch impr. surf.-mtd,isolated input ,lock-differing lockings,W1**

**Technical Features**

**Materials**

Colour	Grey
RAL code	7011

**Controls and indicators**

Venetian blind switch type	2-pole switch
----------------------------	---------------

**Materials**

Surface finish	Matt
Contains recycled material (% of total plastic weight)	0 %
Material	Thermoplastic
Treatment	Untreated

**Voltage**

Rated voltage	240 V
---------------	-------

**Electric current**

Switching current	10 A
Switching current	10 A

**Safety**

Ingress Protection (IP) class	IP55
Locking type	Differing locking

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Texts**

Type of connection	With screw terminals
Installation mode	For screw fastening
Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor

**Connection**

Connector/plug type	Screw terminal
---------------------	----------------

**Equipment**

Is key removable	Yes
------------------	-----

**Suitable for**

cubyko	
--------	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes