



WNC122



Soc.out. earth. pin 2gang hor. hinged cover surf.-mtd, W.1, grey/light grey matt

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current IN	16 A
------------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	76 mm
Width	147 mm
Depth	65 mm
Number of units	2
Built-in depth flush-mounted boxes	0 mm
Built-in depth	65 mm

Connection

Connector/plug type	Screw terminal
Conductor cross-section	1.0 - 2.5 mm ²
Cross-section flexible conductor without wire end sleeve	1.0 - 2.5 mm ²
Number of conduit inlets	2

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	2x socket outlets

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55
Usable in higher IP class	IP55 with closed cover

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Imprint	Without imprint
Cover	For covering of socket outlets
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	Without labelling

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes