



WNC123



IP55



3gang soc.out. earthing pin+hinged cover surface-mtd, W.1, grey/light grey matt

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	76 mm
Width	218 mm
Depth	42.50 mm
Number of units	3
Built-in depth flush-mounted boxes	0 mm
Built-in depth	0 mm

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK08
Ingress Protection (IP) class	IP55

Product Datasheet

WNC123

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free	Yes
RoHS conform	Yes