



WNC123



3gang soc.out. earthing pin+hinged cover surface-mtd, W.1, grey/light grey matt

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	16 A
---------------	------

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	76 mm
Width	218 mm
Depth	42.50 mm
Number of units	3
Built-in depth flush-mounted boxes	0 mm
Built-in depth	65 mm
Height of P-touch band for labelling field	0 mm

Connection

Connector/plug type	Plug-in terminal
Conductor cross-section	1.0 - 2.5 mm ²
Cross-section flexible conductor without wire end sleeve	1.0 - 2.5 mm ²

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
With claw mounting	No
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Earthing pin
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	3x socket outlets

Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
----------------------------------	-----

Impact resistance IK	IK08
----------------------	------

Ingress Protection (IP) class	IP55
-------------------------------	------

Usable in higher IP class	IP55 with closed cover
---------------------------	------------------------

Functions

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
-------	------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	Without labelling
-----------	-------------------

Suitable for

cubyko	
--------	--

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----
