



WNC123B



IP55



**3gang soc.out. earthing pin + hinged cover surf.-mtd, W.1, p.white matt plastic**

### Technical Features

#### Voltage

Rated voltage 250 V

#### Electric current

Rated current 16 A

#### Use conditions

Operating temperature -15 - 30 °C

#### Frequency

Frequency 50 - 60 Hz

#### Materials

Colour Polar white

RAL code 9010

Surface finish Matt

Material Thermoplastic

Treatment Untreated

#### Dimensions

Height 76 mm

Width 218 mm

Depth 22.80 mm

Number of units 3

Built-in depth flush-mounted boxes 0 mm

Built-in depth 0 mm

#### Connection

Connector/plug type Plug-in terminal

#### Installation, mounting

Mounting on Surface mounting

Mounting-/Connection Position Horizontal

#### Connectivity

Type of connection Plug-in connection

Mounting type Screw mounting

#### Equipment

Connector/plug type socket outlet Earthing pin

Rotated central insert No

With hinged lid Yes

With round protective earth pin Yes

With signal lamp No

With lock No

#### Accessories

Has labelling field No

#### Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

#### Capacity

Number of modules 2

#### Safety

With enhanced contact protection Yes

Impact resistance IK IK08

Ingress Protection (IP) class IP55

|                           |                                     |
|---------------------------|-------------------------------------|
| <b>Functions</b>          |                                     |
| With orientation lighting | No                                  |
| With function lighting    | No                                  |
| <b>Identification</b>     |                                     |
| With imprint              | No                                  |
| <b>Texts</b>              |                                     |
| Cover                     | Complete housing                    |
| Protection                | Without enhanced contact protection |
| Type of connection        | With plug-in terminals              |
| <b>Suitable for</b>       |                                     |
| cubyko                    |                                     |
| <b>Sustainability</b>     |                                     |
| Halogen free              | Yes                                 |
| RoHS conform              | Yes                                 |