



WNA021



Push-button insert, change-over contact, illuminated surf/flush-mtd, W.1, grey m LT

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Architecture**

Control/operation element	Rocker
---------------------------	--------

**Materials**

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Contains recycled material (% of total plastic weight)	0 %
Backside internal	Matt

**Dimensions**

Height	55 mm
Width	55 mm
Depth	41 mm
Built-in depth	12 mm
Built-in depth flush-mounted boxes	0 mm
Height of P-touch band for labelling field	0 mm

**Installation, mounting**

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

**Controls and indicators**

Indicator lamp	As an accessory
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

**Connectivity**

With claw mounting	No
--------------------	----

**Connection**

Connector/plug type	Turn screw lock
---------------------	-----------------

**Safety**

Ingress Protection (IP) class	IP55
Impact resistance IK	IK08

**Accessories**

Has labelling field	No
---------------------	----

**Use conditions**

Operating temperature	-25 - 35 °C
-----------------------	-------------

**Texts**

Installation mode	For screw fastening
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Switch mode	Change-over

---

**Texts**

Type of connection

With N-terminal  
With plug-in terminals

---

**Suitable for**

cubyko

---

**Sustainability**

REACH-SVHC free

Yes

RoHS conform

Yes