



WNA021B



Push-button insert, change-over contact, illuminated surf.-/flushmtd, W1, p.wh. LT

Technical Features

Electric current

Momentary contact current

10 A

Voltage

Rated voltage

250 V

Frequency

Frequency

50 - 60 Hz

Architecture

Control/operation element

Rocker

Materials

Colour

Polar white

Surface finish

Matt

Material

Thermoplastic

Treatment

Untreated

Transparent

No

Dimensions

Height

71 mm

Width

71 mm

Depth

43 mm

Built-in depth flush-mounted boxes

0 mm

Installation, mounting

Mounting on

Flush mounting
Surface mounting

Controls and indicators

Number of buttons

1

Type of push button

Single push button

With feedback signal contact

No

Safety

Ingress Protection (IP) class

IP55

Impact resistance IK

IK08

Accessories

Has labelling field

No

Use conditions

Operating temperature

-25 - 35 °C

Texts

Installation mode

For screw fastening

Lighting

With blue 230 V LED unit

For lighting and monitoring circuit

Type of connection

With N-terminal

With plug-in terminals

Suitable for

cubyko

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes