



WNA025B

Push-button insert, NO contact rocker surface-mtd/flush-mtd, W.1, grey matt LT

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Rocker
---------------------------	--------

Materials

Colour	Polar white
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	80 mm
Width	80 mm
Depth	32 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK08

Accessories

Has labelling field	Yes
---------------------	-----

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
Lighting	With blue 230 V LED unit
Terminal	Wago clip-in 3-wire connection terminal for wiring
Type of connection	With N-terminal With plug-in terminals

Suitable for

Hager cubyko	
--------------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes