



WNA044



Push-button insert, 2 NO contacts rocker 2g surf./flushmtd comm. input ,W1, grey

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Double rocker

Materials

Colour Grey
 Surface finish Matt
 Material Thermoplastic
 Treatment Untreated
 Transparent No

Dimensions

Height 71 mm
 Width 71 mm
 Depth 53 mm
 Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
 Surface mounting

Controls and indicators

Indicator lamp As an accessory
 Number of buttons 1
 Type of push button Series push button
 With feedback signal contact No

Safety

Ingress Protection (IP) class IP55
 Impact resistance IK IK08

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Installation mode For screw fastening
 Type of connection With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free Yes
 REACh-SVHC free Yes
 RoHS conform Yes