



WNA044



Push-button insert, 2 NO contacts rocker 2g surf./flushmtd comm. input ,W1, grey

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Double rocker

Materials

Colour Grey
 Surface finish Matt
 Material Thermoplastic
 Treatment Untreated
 Transparent No

Dimensions

Height 71 mm
 Width 71 mm
 Depth 53 mm
 Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
 Surface mounting

Controls and indicators

Indicator lamp As an accessory
 Number of buttons 1
 Type of push button Series push button
 With feedback signal contact No

Connection

Connector/plug type Turn screw lock

Safety

Ingress Protection (IP) class IP55
 Impact resistance IK IK08

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Installation mode For screw fastening
 Type of connection With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free Yes
 REACh-SVHC free Yes
 RoHS conform Yes