



WNA044B



Push-button insert, NOcontact rocker surf.-mtd/flush-mtd, W.1, p.white m plus LT

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Double rocker

Materials

Colour Polar white

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 71 mm

Width 71 mm

Depth 42 mm

Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Controls and indicators

Indicator lamp As an accessory

Number of buttons 1

Type of push button Series push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK08

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Installation mode For screw fastening

Type of connection With plug-in terminals

Suitable for

cubyko

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes