



WNA301B



**Blind push-b. insert rocker 2g+impr.ed symb.arrow surf.-/flushmtd,W.1,p.wh. LT**

**Technical Features**

**Electric current**

Momentary contact current

10 A

**Voltage**

Rated voltage

250 V

**Frequency**

Frequency

50 - 60 Hz

**Architecture**

Control/operation element

Double rocker

**Materials**

Colour

Polar white

Surface finish

Matt

Material

Thermoplastic

Treatment

Untreated

Transparent

No

**Dimensions**

Height

75 mm

Width

75 mm

Depth

32 mm

Built-in depth flush-mounted boxes

0 mm

**Installation, mounting**

Mounting on

Flush mounting  
Surface mounting

**Controls and indicators**

Number of buttons

2

Type of push button

Single push button

With feedback signal contact

No

**Safety**

Ingress Protection (IP) class

IP20

Impact resistance IK

IK08

**Accessories**

Has labelling field

No

**Use conditions**

Operating temperature

-25 - 35 °C

**Texts**

Imprint

With imprinted symbol arrow

Installation mode

For screw fastening

Switch mode

With mechanical and electrical interlock to prevent mutual activation

Type of connection

With plug-in terminals

**Suitable for**

cubyko

**Sustainability**

Halogen free

Yes

REACH-SVHC free

Yes

RoHS conform

Yes