



WNC025



IP55



**Push-button, change-over contact surface-mtd, W1, grey/light grey matt LT**

**Technical Features**

**Electric current**

Momentary contact current

10 A

**Voltage**

Rated voltage

250 V

**Frequency**

Frequency

50 - 60 Hz

**Architecture**

Control/operation element

Single rocker

Number of poles

1

**Materials**

Colour

Grey

Surface finish

Matt

Material

Thermoplastic

Treatment

Untreated

Transparent

No

Backside internal

Mat

**Dimensions**

Height

55.50 mm

Width

55.50 mm

Depth

27.80 mm

Built-in depth flush-mounted boxes

0 mm

Height of P-touch band for labelling field

12 mm

**Installation, mounting**

Mounting on

Surface mounting

**Controls and indicators**

Number of buttons

1

Type of push button

Single push button

With feedback signal contact

No

**Safety**

Ingress Protection (IP) class

IP55

Impact resistance IK

IK08

**Accessories**

Has labelling field

Yes

**Use conditions**

Operating temperature

-25 - 35 °C

**Texts**

Installation mode

For screw fastening

Lighting

With blue 230 V LED unit

Sealing

With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Terminal

With Wago clip-in 2-wire connection terminal for wiring  
With two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection

With N-terminal

With plug-in terminals

**Suitable for**

cubyko

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |