



WNC025



IP55



Push-button, change-over contact surface-mtd, W.1, grey/light grey matt LT

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Single rocker

Number of poles 1

Materials

Colour Grey

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Backside internal Matt

Dimensions

Height 55.50 mm

Width 55.50 mm

Depth 27.80 mm

Built-in depth flush-mounted boxes 0 mm

Height of P-touch band for labelling field 12 mm

Installation, mounting

Mounting on Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK08

Accessories

Has labelling field Yes

Use conditions

Operating temperature -25 - 35 °C

Texts

Installation mode For screw fastening

Lighting With blue 230 V LED unit

Sealing With full-face sealing on the rear side of housing for cable entry and surface adjustment on the backside

Terminal With Wago clip-in 2-wire connection terminal for wiring
With two clip-in places for Wago 2-wire connection terminals in the housing floor

Type of connection With N-terminal
With plug-in terminals

Suitable for

cubyko

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
