



HWX006H

**Spring charging motor 415-450V AC 50/60Hz HW1 (MO)**

**Technical Features**

**Electric current**

|               |        |
|---------------|--------|
| Rated current | 0.50 A |
|---------------|--------|

**Voltage**

|   |             |
|---|-------------|
| Type voltage supply                       | AC          |
| Rated insulation voltage $U_i$            | 450 V       |
| Rated impulse withstand voltage $U_{imp}$ | 6000 V      |
| Command voltage AC                        | 415 - 450 V |

**Use conditions**

|                       |             |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |