



HWX011H

Spring charging motor 24V AC 50/60Hz HW2/4 (MO)

Technical Features

Electric current

Rated current	8.20 A
---------------	--------

Voltage

Type voltage supply	AC
Rated insulation voltage Ui	450 V
Rated impulse withstand voltage Uimp	6000 V
Command voltage AC	24 - 24 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

With auto reset function	No
--------------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes