



HWX040H

Auxiliary Switch HW1 (AX)

Technical Features

Electric current

| | |
|--------------------------|-----|
| Rated current 230 V AC15 | 4 A |
|--------------------------|-----|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Click mounting |
|---------------|----------------|

Connection

| | |
|------------------|---------------|
| Type of contacts | 1x changeover |
|------------------|---------------|

Voltage

| | |
|---|--------|
| Rated insulation voltage U_i | 690 V |
| Rated impulse withstand voltage U_{imp} | 1500 V |
| Type voltage supply | AC/DC |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Endurance

| | |
|---------------------------------|-------|
| Number of mechanical operations | 15000 |
|---------------------------------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 70 °C |
|-----------------------|-------------|

Endurance

| | |
|--|------|
| Electric endurance in number of cycles | 3025 |
|--|------|

Use conditions

| | |
|-------------------------------|-------------|
| Storage/transport temperature | -40 - 70 °C |
|-------------------------------|-------------|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 0 W |
|---------------------------|-----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |