



HWX041H

**Auxiliary Switch low-level HW1 (AX)**

**Technical Features**

**Electric current**

Rated current 230 V AC15 2 A

**Connectivity**

Mounting type Click mounting

**Connection**

Type of contacts 1x changeover

**Voltage**

Rated insulation voltage  $U_i$  690 V

Rated impulse withstand voltage  $U_{imp}$  1500 V

Type voltage supply AC/DC

**Frequency**

Frequency 50 - 60 Hz

**Endurance**

Number of mechanical operations 15000

**Use conditions**

Operating temperature -25 - 70 °C

**Endurance**

Electric endurance in number of cycles 3025

**Use conditions**

Storage/transport temperature -40 - 70 °C

**Power**

Total power loss under IN 0 W

**Safety**

Ingress Protection (IP) class IP4X

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes