



HWX714H

Spring charging motor 200-250V DC HW2/4 (MO)

Technical Features

Electric current

Rated current I _N	1 A
------------------------------	-----

Voltage

Type voltage supply	DC
Rated insulation voltage U _i	450 V
Rated impulse withstand voltage U _{imp}	6000 V
Command voltage DC	200 - 250 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Functions

With auto reset function	No
--------------------------	----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes