



14103505



FCC soc.out. insert 8/8p shielded hinged cover surf./flushmtd,cat.6,labfield,W1

Technical Features

Frequency

Transmission bandwidth 500 - 500 MHz

Equipment

Number of outputs 2

Use conditions

Operating temperature -15 - 30 °C

Materials

Colour Grey

Connection

Connector/plug type Cutting terminal

Materials

Material Thermoplastic

Safety

Ingress Protection (IP) class IP20

Dimensions

Height of P-touch band for labelling field 12 mm

Texts

Outlet With straight outlet

Voltage Suitable for PoE+

Installation mode Without spreader claws

Protection With self-closing dust protection cover per jack

Type of connection With cutting terminals

Sustainability

REACH-SVHC free Yes

RoHS conform Yes