



14093505



FCC soc.out. 8p shielded hinged cover surf.-mtd, cat.6, lab. field,W.1, grey matt

**Technical Features**

**Frequency**

Transmission bandwidth 500 - 500 MHz

**Equipment**

Number of outputs 1

**Use conditions**

Operating temperature -15 - 30 °C

**Equipment**

With hinged lid Yes

**Materials**

Colour Grey

**Connection**

Connector/plug type UAE/IAE (ISDN)

**Materials**

Material Thermoplastic

**Safety**

Ingress Protection (IP) class IP55

**Dimensions**

Height of P-touch band for labelling field 12 mm

**Texts**

Outlet With 45° oblique outlet

Voltage Suitable for PoE+

Installation mode For screw fastening  
Without spreader claws

Protection With self-closing dust protection cover before jack

Type of connection With cutting terminals

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes