



14093502



FCC soc.out. 8p shielded hinged cover surf.-mtd,cat.6,lab.field,W.1,p.wh.m.plas.

Technical Features

Frequency

Transmission bandwidth500 - 500 MHz

Equipment

Number of outputs1

Use conditions

Operating temperature-15 - 30 °C

Equipment

With hinged lidYes

Materials

ColourPolar white

Connection

Connector/plug typeUAE/IAE (ISDN)

Materials

MaterialThermoplastic

Safety

Ingress Protection (IP) classIP55

Texts

Installation modeFor screw fastening
Without spreader claws

Type of connectionWith cutting terminals

VoltageSuitable for PoE+

Sustainability

REACH-SVHC freeYes

RoHS conformYes