



FWB42M2

**FWB encl. univers,IP44,class II, 4x26mod.,650x550x161mm,QuickConnect**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	4
Number of rows	4
Number of section in width	2
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	104
-------------------	-----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	650 mm
Width	550 mm
Depth	165 mm
Built-in height	650 mm
Built-in width	550 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	161 mm
----------------	--------

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	26
-----------------------	----

**Cover, door**

Type of handle	Hinged pattern handle
Door/cover is transparent	No
Cabinet door type	Single door

**Connection**

Number of conduit inlets	8
--------------------------	---

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Bar lock

---

**Sustainability**

---

RoHS conform

Yes