



FWB42S

FWB encl. univers,4-rows 96 modules cl.II IP44 w.plain door, 650x550x161mm,QC

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	8
Number of rows	4
Number of section in width	2
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	96
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	650 mm
Width	550 mm
Depth	165 mm
Built-in height	650 mm
Built-in width	550 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	161 mm
----------------	--------

Cover, door

Number of locks	1
-----------------	---

Dimensions

Number of width units	24
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No
Cabinet door type	Single door

Connection

Number of conduit inlets	8
--------------------------	---

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock

Sustainability

RoHS conform	Yes
--------------	-----