



FWB62S

FWB encl.,univers,6-rows 144 modules cl.II IP44 w.plain door, 950x500x161mm,QC

Technical Features

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Equipment

| | |
|----------------------------|-----|
| Number of rails | 12 |
| Number of rows | 6 |
| Number of section in width | 2 |
| With lock | No |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|-----|
| Number of modules | 144 |
|-------------------|-----|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | No |
| With conduit inlets | Yes |

Dimensions

| | |
|-----------------|--------|
| Height | 950 mm |
| Width | 550 mm |
| Depth | 165 mm |
| Built-in height | 950 mm |
| Built-in width | 550 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

Dimensions

| | |
|----------------|------|
| Built-in depth | 0 mm |
|----------------|------|

Cover, door

| | |
|-----------------|---|
| Number of locks | 1 |
|-----------------|---|

Dimensions

| | |
|-----------------------|----|
| Number of width units | 24 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-----------------------|
| Type of handle | Hinged pattern handle |
| Door/cover is transparent | No |
| Cabinet door type | Single door |

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 8 |
|--------------------------|---|

Connectivity

| | |
|---------------|------------------|
| Mounting type | Surface mounting |
|---------------|------------------|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK09 |
| Ingress Protection (IP) class | IP44 |
| Locking type | Without lock |
| Glow wire test | 750 °C |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|