



FWB73S

FWB encl.,univers,7-rows 252 modules cl.II IP44 w.plain door, 1100x800x161mm,QC

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	21
Number of rows	0
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	252
-------------------	-----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	1100 mm
Width	800 mm
Depth	165 mm
Built-in height	1100 mm
Built-in width	800 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	161 mm
----------------	--------

Cover, door

Number of locks	1
-----------------	---

Dimensions

Number of width units	36
-----------------------	----

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connection

Number of conduit inlets	12
--------------------------	----

Connectivity

Mounting type	Surface mounting
---------------	------------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Without lock

Sustainability

RoHS conform	Yes
--------------	-----