



FP63TN2

Enclosure, univers, IP44, CL 1, 950x800x205mm, empty

Technical Features

Dimensions

Height	950 mm
Width	800 mm
Depth	205 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP44
Protection class	Isolation class I
Locking type	Bar lock Without lock
Impact resistance IK	IK09

Equipment

Number of section in width	3
Number of flange plate openings	6

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Steel

Equipment

Number of rows	6
----------------	---

Materials

Surface finish	Matt
----------------	------

Cover, door

Number of cabinet doors	2
Number of locks	1
Door/cover is transparent	No
Cabinet door type	Single door

Electric current

Rated current IN	250 A
------------------	-------

Sustainability

RoHS conform	Yes
--------------	-----