



WBM32R

#### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

|                |        |
|----------------|--------|
| Surface finish | Glossy |
|----------------|--------|

##### Identification

|                      |  |
|----------------------|--|
| Assembly arrangement | Basic element with central cover plate |
|----------------------|--|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Dimensions

|            |            |
|------------|------------|
| Dimensions | 27 x 27 mm |
|------------|------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

##### Connection

|                     |          |
|---------------------|----------|
| Connector/plug type | RotoLoc® |
|---------------------|----------|

##### Texts

|                   |          |
|-------------------|----------|
| Installation mode | RotoLoc® |
|-------------------|----------|

|                    |                      |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

|          |                        |
|----------|------------------------|
| Lighting | For monitoring circuit |
|----------|------------------------|

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

##### Sustainability

|              |     |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|