Product Datasheet
WBSP1S-MB



WBSP1S-MB

Technical Features

Electric current

Rated current IN	10 A

Frequency

Frequency	50 - 50 Hz

Materials

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

Dimensions

Height	77 mm
Width	117 mm
Depth	28 mm
Number of units	1
Built-in depth	23 mm

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

Accessories

Has labelling field	No

Cover, door

Type of lid	Without lid

Capacity

Number of modules	1

Safety

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No

Texts

Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

Sustainability

Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes