



WBSP1VS

### Technical Features

#### Electric current

Rated current	10 A
---------------	------

#### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

#### Dimensions

Height	77 mm
Width	117 mm
Depth	28 mm
Built-in depth	23 mm

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	1
-------------------	---

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

#### Suitable for

silhouette	
------------	--

#### Sustainability

RoHS conform	Yes
--------------	-----