



WBSP1VS

Technical Features

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Dimensions

Height 77 mm

Width 117 mm

Depth 28 mm

Built-in depth 23 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Full cover plate

Protection Enhanced contact protection

Type of connection With screw terminals

Suitable for

silhouette

Sustainability

Halogen free Yes

RoHS conform Yes