



WBSP1VS-MW

**Technical Features**

**Electric current**

Rated current 10 A

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour White

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

**Dimensions**

Height 77 mm

Width 117 mm

Depth 28 mm

Built-in depth 23 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting

**Equipment**

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Full cover plate

Protection Enhanced contact protection

Type of connection With screw terminals

**Sustainability**

Halogen free Yes

RoHS conform Yes