



WBSP1VS-MW

**Technical Features**

**Electric current**

Rated current	10 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

**Dimensions**

Height	77 mm
Width	117 mm
Depth	28 mm
Built-in depth	23 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

**Sustainability**

Halogen free	Yes
RoHS conform	Yes