



WBSSV5-MB

**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour Black

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 5

**Dimensions**

Dimensions 117 x 77 mm

Built-in depth 23 mm

**Electric current**

Rated current 16 A

**Texts**

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Push button No

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes