



WBWSH1

Premiere 1G IP66 horz switch

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	77 x 117 mm
Built-in depth	25 mm

**Safety**

Ingress Protection (IP) class	IP66
-------------------------------	------

**Electric current**

Rated current	16 A
---------------	------

**Texts**

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes