



WBWSV4

Premiere 4G IP66 vert switch

Technical Features

Installation, mounting

Mounting on Flush mounting

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 4

Dimensions

Dimensions 117 x 77 mm

Built-in depth 25 mm

Electric current

Rated current 16 A

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Push button No

Sustainability

REACH-SVHC free Yes

RoHS conform Yes