



EER505

**Motion detector corridor 360° flush-mounted NO contact detection 5x30m**

**Technical Features**

**Detection**

Detection angle	360 - 360
Type of sensor	Movement detector
Detection angle horizontal	360 - 360

**Lighting**

LED lamp power	400 W
Photocell sensitivity	5 - 2000 lx

**Settings**

Switch off delay time	0 s
Switch on delay time	0 s

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Built-in depth	78 mm
Installation height	2.50 - 2.50 m

**Materials**

Material	Plastic
Surface finish	Matt

**Safety**

Ingress Protection (IP) class	IP41
-------------------------------	------

**Installation, mounting**

Mounting on	Flush mounting
Ceiling mounting possible	Yes

**Reach distance**

Max. transmission range frontally	5 m
Max. transmission range sideways	10 m

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes