



EER515

Motion detector corridor 360° surface mounted NO contact detection 5x30m

Technical Features

Detection

Detection angle	360 - 360
Type of sensor	Movement detector
Detection angle horizontal	0 - 0

Lighting

LED lamp power	400 W
Photocell sensitivity	5 - 2000 lx

Settings

Switch off delay time	0 s
Switch on delay time	0 s

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Built-in depth	78 mm
Installation height	2.50 - 2.50 m

Materials

Material	Plastic
Surface finish	Matt

Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Ceiling mounting possible	Yes

Reach distance

Max. transmission range frontally	5 m
Max. transmission range sideways	10 m

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes