



EER518

Motion detector highbay 360° surface mounted NO contact detection height 8m

Technical Features

Detection

Detection angle	360 - 360 °
Type of sensor	Movement detector
Detection angle horizontal	360 - 360

Settings

Time delay	1 Min - 1 h
Minimal duty cycle	2 s

Lighting

Response brightness adjustable	5- 2000 lx
--------------------------------	------------

Settings

Response brightness adjustable	Yes
--------------------------------	-----

Lighting

LED lamp power	400 W
----------------	-------

Settings

Response sensitivity adjustable	Yes
---------------------------------	-----

Lighting

Photocell sensitivity	5 - 2000 lx
-----------------------	-------------

Settings

Switch on delay time	0 s
----------------------	-----

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Dimensions

Built-in depth	78 mm
Recommended installation height	6 - 9 m
Installation height	6- 10 m

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Materials

Material	Plastic
Surface finish	Matt

Safety

Ingress Protection (IP) class	IP41
-------------------------------	------

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No
Ceiling mounting possible	Yes

Power supply

Supply voltage	230 V +10%/-15%
----------------	-----------------

Reach distance

Max. transmission range frontally	7 m
Max. transmission range sideways	11 m

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes