



EER518

**Motion detector highbay 360° surface mounted NO contact detection height 8m**

**Technical Features**

**Detection**

Detection angle	360 - 360 °
Type of sensor	Movement detector
Detection angle horizontal	360 - 360

**Settings**

Time delay	1 Min - 1 h
Minimal duty cycle	2 s

**Lighting**

Response brightness adjustable	5- 2000 lx
--------------------------------	------------

**Settings**

Response brightness adjustable	Yes
--------------------------------	-----

**Lighting**

LED lamp power	400 W
----------------	-------

**Settings**

Response sensitivity adjustable	Yes
---------------------------------	-----

**Lighting**

Photocell sensitivity	5 - 2000 lx
-----------------------	-------------

**Settings**

Switch on delay time	0 s
----------------------	-----

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Built-in depth	78 mm
Recommended installation height	6 - 9 m
Installation height	6- 10 m

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Material	Plastic
Surface finish	Matt

**Safety**

Ingress Protection (IP) class	IP41
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No
Ceiling mounting possible	Yes

**Power supply**

Supply voltage	230 V +10%/-15%
----------------	-----------------

**Reach distance**

Max. transmission range frontally	7 m
Max. transmission range sideways	11 m

---

**Sustainability**

---

REACH-SVHC free	Yes
RoHS conform	Yes

---